



**Catalog No. 9T11C1004G33**

**Description: 3C,75KVA,480-208Y,115C,N2,K13,ES,DOE**

**UPC No 783173906354**

**Home > Transformers > Dry Type Vented > K-Factor**

ABB's K-Factor transformers are designed to withstand the additional heating that accompanies the presence of harmonics in electrical systems. K-Factor transformers are designed not to eliminate harmonics, but to withstand their negative effects. They are available with aluminum or copper windings and in all three temperature rise ratings. K-Factor transformers meet DOE 2016 efficiency standards and are UL Listed and Energy Verified. Qualified to the seismic requirements of IEEE-693-2005 and the IBC-2021 and CBC 2022.

**Descriptors**

Category	K-Factor
----------	----------

**Specifications**

TransType	QL
Phase	3
PriVoltage	480
SecVoltage	208Y/120
KVA	75 KVA
Coil Material	CU
TempRise	115 °C
Frequency	60 Hz
AmbTemp	40 °C
EnergyEfficiency	DOE 2016
KFactor	K13
Enclosure Type	NEMA 2
Sound	Std

**Classifications**

UL	Yes
----	-----