



**Catalog No. 9T21B4553G02**

**Description: 1A,10kVA,240-120,115C,3R,60Hz,QMS**

**UPC No 783173030455**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost Autotransformer**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

Category	Buck Boost Autotransformer
GO Schedule	T7

**Specifications**

Phase	1
PriVoltage	240
SecVoltage	120
KVA	10 KVA
Coil Material	AL
TempRise	115 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
FrameSize	16350
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

**Classifications**

UL	Yes
cUL	Yes