



**Catalog No. 9T51B0145**

**Description: 1C,5KVA,133-120,100C,3R,60HZ,BB,AXF,QB**

**UPC No 783173009093**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost Autotransformer**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

Category	Buck Boost Autotransformer
GO Schedule	T5

**Specifications**

Phase	1
PriVoltage	133
SecVoltage	120
KVA	5 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
FrameSize	10225
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

**Classifications**

UL	Yes
cUL	Yes