



Representative Image

Catalog No. 9T51B0143

Description: 1C,2KVA,133-120,55C,3R,60HZ,BB,AXF,QB

UPC No 783173036617

Home > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost Autotransformer

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Buck Boost Autotransformer
GO Schedule	T5

Specifications

Phase	1
PriVoltage	133
SecVoltage	120
KVA	2 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
FrameSize	8175
TempClass	105 °C
AmbTemp	40 °C
InsulSys	CLASSA
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes