



Image représentative

n° de catalogue 9T51B0150

Description: 1C,2KVA,139-120,100C,3R,60HZ,BB,AXF,QB

UPC No 783173036655

Accueil > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost Autotransformer

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descripteurs

Catégorie	Buck Boost Autotransformer
GO Schedule	T5

Spécifications

Phase	1
PriVoltage	139
SecVoltage	120
KVA	2 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
FrameSize	8175
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes