

Representative Image

Catalog No. 9T58K0049G09

Description: 1C,0.375kVA,230x460-115,100,C&C,1/4FC,IP

UPC No 783173195291

Home > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool

ABB's Machine tool core and coil transformers are isolation transformers designed to provide a high degree of secondary voltage stability (regulation) during a brief period of overload condition (also referred to as “inrush current”). They are ideal for applications where power regulation and space optimization are critical. Machine tool core and coil transformers feature welded cores to deliver outstanding performance, long life, and quiet operation.

Descriptors

Category	Machine Tool
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	230x460
SecVoltage	115
KVA	0.375 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Sub Type	Machine Tool Terminal Blk
Frequency	60 Hz
FrameSize	8250
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
SecRatingType	1
Outline	303B947AAP08250
TransType	IP

Classifications

UL	Yes
cUL	Yes