



Image représentative

## n° de catalogue 9T58K0051

Description: 1C,0.75KVA,240X480-120,80C,C&C,TB,IP

UPC No 783173151099

Accueil > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool

ABB's Machine tool core and coil transformers are isolation transformers designed to provide a high degree of secondary voltage stability (regulation) during a brief period of overload condition (also referred to as "inrush current"). They are ideal for applications where power regulation and space optimization are critical. Machine tool core and coil transformers feature welded cores to deliver outstanding performance, long life, and quiet operation.

### Descripteurs

Catégorie	Machine Tool
GO Schedule	TQ

### Spécifications

Phase	1
PriVoltage	240x480
SecVoltage	115
KVA	0.75 KVA
Coil Material	CU
TempRise	80 °C
ElecShield	N
Sub Type	Machine Tool Terminal Blk
Frequency	60 Hz
FrameSize	12225
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
Outline	303B947AAP12225
TransType	IP

### Classifications

UL	Yes
cUL	Yes