

Catalog No. 9T58K0082

Description: 1C,0.05KVA,380>208-115/95,55C,C&C,TB,IP

UPC No 783173120965

Home > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool

ABB's Machine tool core and coil transformers are isolation transformers designed to provide a high degree of secondary voltage stability (regulation) during a brief period of overload condition (also referred to as "inrush current"). They are ideal for applications where power regulation and space optimization are critical. Machine tool core and coil transformers feature welded cores to deliver outstanding performance, long life, and quiet operation.



Representative Image

Descriptors

Category	Machine Tool
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	208/277/380
SecVoltage	115/95
KVA	0.05 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	Machine Tool Terminal Blk
Frequency	50 Hz
FrameSize	6150
TempClass	105 °C
AmbTemp	40 °C
InsulSys	CLASSA
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
Outline	303B947AAP06150
TransType	IP

Classifications

UL	Yes
cUL	Yes