



Image représentative

n° de catalogue 9T58K0501

Description: 1C,0.06kVA,480-120,55C,C&C,CLO,60Hz,IP

UPC No 783173203217

Accueil > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

ABB's Machine tool core and coil transformers are isolation transformers designed to provide a high degree of secondary voltage stability (regulation) during a brief period of overload condition (also referred to as "inrush current"). They are ideal for applications where power regulation and space optimization are critical. Machine tool core and coil transformers feature welded cores to deliver outstanding performance, long life, and quiet operation.

Descripteurs

Catégorie	Control Power
GO Schedule	TQ

Spécifications

Phase	1
PriVoltage	480
SecVoltage	120
KVA	0.06 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	CONTROL LEADS OUT
Frequency	60 Hz
FrameSize	6100
TempClass	105 °C
AmbTemp	40 °C
InsulSys	CLASSA
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
Outline	303B947ABP06100
TransType	IP

Classifications

UL	Yes
cUL	Yes