

Catalog No. ELL5221/2-G

Description: PVC CTD ELBOW 22.5D 5IN STEEL GRAY

UPC No 704508029425

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 5 Inch/129 Metric, Angle 22.5 Degrees, Radius 24 Inch/609.60 Millimeters, Offset 31 Inch/787.40 Millimeters, Straight End 7 Inch/177.80 Millimeters, Unbent Length 51.70 Inch/1,313.16 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Representative Image

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	51.70 in , 1,313.16 mm
Trade Size	5 in , 129 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid

by ABB

ETIM	EC001493 Bend for cable protection tubes
Shape	Outer - and inner side plain
Inner diameter	129 mm
Angle of bow	22.5 °