



Representative Image

Catalog No. 9T58K4350

Description: 1C,0.75kVA,120/240-12/24,55C,50/60,TB,IP

UPC No 783173825747

Home > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool

ABB's Machine tool core and coil transformers are isolation transformers designed to provide a high degree of secondary voltage stability (regulation) during a brief period of overload condition (also referred to as "inrush current"). They are ideal for applications where power regulation and space optimization are critical. Machine tool core and coil transformers feature welded cores to deliver outstanding performance, long life, and quiet operation.

Descriptors

Category	Machine Tool
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	120/240
SecVoltage	12/24
KVA	0.08 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	Machine Tool Terminal Blk
Frequency	50 Hz
FrameSize	8100
TempClass	105 °C
AmbTemp	40 °C
InsulSys	CLASSA
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
Outline	303B947AAP08100
TransType	IP

Classifications

UL	Yes
cUL	Yes