

Representative Image

Catalog No. CR151KFC04E

Description: Terminal Blocks, DIN-Rail Mounting, Feed Through, Box

UPC No

Home > Terminal Blocks > NEMA > Terminal Blocks

DIN-Rail Mounted Terminal Blocks -Feed Through Blocks - Box or Collar Type Terminals -Five circuits per inch give total of 12 circuits in 2.4 inch long terminal block, equal to European 5 mm spacing. -Voltage/current ratings: 300 Volt rating: 20 A, 600 Volt rating: 5A. -Larger screws can take torque of standard screwdriver.- Larger, easier-to-wire openings take one 12 or two 14 wires. -Multi-circuit jumper available. -Unique staggered design helps keep loose strands from shorting adjacent poles. -One-piece designno end barriers and clips needed. -Extra wide marking area for pressure sensitive tape permits printing or marking prior to assembly, sliding marker design permits easy access to all screws. -Universal mountingfits all standard GE rails and mini DIN-rails. C04E 30 A

Descriptors

Category	Terminal Blocks
Fastrac	No
GO Schedule	GO-10G5

Specifications

Product Type	Terminal Blocks
Mounting Style	Aluminum Mounting Rail
Function	Terminal Block
Termination Type	Box
Amperage	30 A
Points per Block	4
Wire Size	#22-10
Product Prefix	CR151K
Voltage	300
UL Reference File E	40800
Series Prefix	CR151K

Classifications

C-UL/CSA Cert. LR	AP53842

by ABB