

Representative Image

Catalog No. ELL3/4221/2-G

Description: PVC CTD ELBOW 22.5D 3/4IN STEEL GRY

UPC No 704508036324

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 3/4 Inch/21 Metric, Angle 22.5 Degrees, Radius 4-1/2 Inch/114.30 Millimeters, Offset 6-1/2 Inch/165.10 Millimeters, Straight End 2 Inch/50.80 Millimeters, Unbent Length 11.07 Inch/281.14 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	PVC Coated for Corrosion Resistance
Application	Connecting Two Pieces of Conduit at a 22.5 Degree Angle

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal

Dimensions

Length	11.07 in , 281.14 mm
Size	3/4 Inch/21mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid

by ABB

ETIM	EC001493 Bend for cable protection tubes
Shape	Outer - and inner side plain
Inner diameter	21 mm
Angle of bow	22.5 °