



Representative Image

Alternate Catalog No. BC6-30-01-P2.4 Catalog No. GJL1213009R5011

Description: BC6-30-01-P-2.4-51 Mini Contactor 17-32VDC, 2.4W

UPC No 4013614053405

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

The BC6-30-01-P mini contactor is a compact 3 pole contactor with 1 auxiliary contact and soldering pins. They are ideally suited for applications where reliability is a must and space is at a premium. Mini contactors are used in residential buildings, commercial buildings and industrial applications for the control of single or three-phase loads up to 4 kW (AC-3) and 20 A / 690 V (AC-1) or switching of control signals. Due to the low coil consumption, this device can be directly controlled by a PLC. Further features are the noiseless and hum-free coil and a switch position indication.

Descriptors

| | |
|----------|---------------|
| Category | AF Contactors |
|----------|---------------|

Specifications

| | |
|--|--|
| Product Type | Mini Contactors (B6, B7) |
| General Use Rating UL/CSA | (300 V AC) 8 A |
| Object Classification Code | Q |
| Terminal Type | Soldering Pins |
| Rated Control Circuit Voltage | 17 ... 32 V DC |
| Number of Main Contacts NO | 3 |
| Number of Main Contacts NC | 0 |
| Maximum Operating Voltage UL/CSA | Main Circuit 600 V AC |
| Resistance to Vibrations acc. to IEC 60068-2-6 | 5g / 5 ... 150 Hz |
| Number of Auxiliary Contacts NO | 0 |
| RoHS Status | Following EU Directive 2011/65/EU |
| Reference Ambient Air Temperature | Operation -20 ... +55 °C |
| Rated Operational Voltage | Auxiliary Circuit 12 ... 240 V DC Auxiliary Circuit 12 ... 500 V AC / DC Main Circuit 12 ... 690 V AC / DC Main Circuit 690 V AC |
| Resistance to Shock acc. to IEC 60068-2-27 | 11 ms Pulse 15g |
| Number of Auxiliary Contacts NC | 1 |
| Maximum Operating Altitude Permissible | 2000 m |
| Rated Operational Current AC-1 | (220 / 240 V) 40 °C 12 A (220 / 240 V) 55 °C 12 A (380 / 440 V) 40 °C 12 A (380 / 440 V) 55 °C 12 A (690 V) 40 °C 6 A (690 V) 55 °C 6 A |
| Standards | IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 |
| Rated Operational Power AC-3 | (220 / 230 / 240 V) 2.2 kW (400 V) 4 kW (400 V) Three Phase 4 kW (440 V) 4 kW (500 V) 4 kW (690 V) 3 kW |

Specifications

| | |
|--|--|
| Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1 | 8 x I _e / AC-3 |
| Horsepower Rating UL/CSA | (208 V AC) Three Phase 1 hp (220 ... 240 V AC) Single Phase 0.5 hp (220 ... 240 V AC) Three Phase 2 hp (440 ... 480 V AC) Three Phase 3 hp (550 ... 600 V AC) Three Phase 1 hp |
| Conventional Free-air Thermal Current | Main Circuit 12 A |
| Rated Operational Current AC-15 | (120 V) 4 A (220 / 240 V) 4 A (24 V) 4 A (380 / 400 V) 3 A (500 V) 2 A |
| Rated Frequency | Control Circuit DC Main Circuit 60 Hz Main Circuit 50Hz Main Circuit DC |
| Rated Short-time Withstand Current | at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 64 A |
| Rated Operational Current AC-3 | (220 / 230 / 240 V) 55 °C 8.5 A (380 / 400 V) 55 °C 8.5 A (440 V) 55 °C 7.4 A (500 V) 55 °C 6.8 A (690 V) 55 °C 3.8 A |
| Rated Making Capacity AC-3 acc. to IEC 60947-4-1 | 10 x I _e / AC-3 |
| Maximum Electrical Switching Frequency | AC-1 300 cycles per hour AC-15 600 cycles per hour AC-3 600 cycles per hour DC-1 600 cycles per hour DC-13 600 cycles per hour DC-3 600 cycles per hour |
| Short-Circuit Protective Devices | gG Type Fuses Type 1 25 A |
| Rated Insulation Voltage | 690 V acc. to UL/CSA 600 V |
| Mechanical Durability | 10000000 cycle |
| Coil Operating Limits | (acc. to IEC 60947-4-1) for DC supply U _c Min. ... U _c Max. (at θ ≤ 55 °C) |
| Secondary Rated Impulse Withstand Voltage | Auxiliary Circuit 6 kV Main Circuit 6 kV |
| Rated Operational Current DC-13 | (110 V) 0.7 A (220 / 240 V) 0.4 A (24 V) 2.5 A |
| Coil Consumption | Average Holding Value DC 2.4 W Average Pull-in Value DC 2.4 W |
| Degree of Protection | Auxiliary Circuit Terminals IP20 Control Circuit Terminals IP20 Main Circuit Terminals IP20 |
| Mounting on DIN Rail | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Screw Terminal Type | Soldering Pins |

Classifications

| | |
|----------|---|
| ETIM 4 | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0 | EC000066 - Power contactor, AC switching |
| ETIM 7 | EC000066 - Power contactor, AC switching |
| ETIM 5.0 | EC000066 - Magnet contactor, AC-switching |
| eClass | 7.0 27371003 |

Dimensions

| | |
|----------------------------|---------|
| Product Net Weight | 0.17 kg |
| Product Net Depth / Length | 51.5 mm |
| Product Net Width | 47.5 mm |
| Product Net Height | 45.5 mm |

Package Information

| | |
|--------------------------------|---------------|
| Package Level 1 Width | 108 mm |
| Package Level 1 Height | 69 mm |
| Package Level 1 Depth / Length | 247 mm |
| Package Level 1 EAN | 4013614415166 |
| Package Level 1 Units | 10 piece |
| Package Level 1 Gross Weight | 1.775 kg |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 |
| Customs Tariff Number | 85365080 |