



Representative Image

Alternate Catalog No. B7-40-00-P01 Catalog No. GJL1311209R0001

Description: B7-40-00-P-01 Mini Contactor 24V 40-450Hz

UPC No 4013614326714

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

The B7-40-00-P mini contactor is a compact 4 pole contactor with soldering pins. They are ideally suited for applications where reliability is a must and space is at a premium. Mini contactors are used in residential buildings, commercial buildings and industrial applications for the control of single or three-phase loads up to 5.5 kW (AC-3) and 20 A / 690 V (AC-1) or switching of control signals. Further features are the silent coil, a switch position indication and the integrated possibility for rail mounting.

Descriptors

| | |
|----------|---------------|
| Category | AF Contactors |
|----------|---------------|

Specifications

| | |
|--|--|
| Product Type | Mini Contactors (B6, B7) |
| General Use Rating UL/CSA | (600 V AC) 16 A |
| Object Classification Code | Q |
| Terminal Type | Soldering Pins |
| Rated Control Circuit Voltage | 24 V AC |
| Number of Main Contacts NO | 4 |
| Number of Main Contacts NC | 0 |
| Maximum Operating Voltage UL/CSA | Main Circuit 600 V AC |
| Resistance to Vibrations acc. to IEC 60068-2-6 | 5g / 5 ... 150 Hz |
| Number of Auxiliary Contacts NO | 0 |
| RoHS Status | Following EU Directive 2011/65/EU |
| Reference Ambient Air Temperature | Operation -25 ... +55 °C |
| Rated Operational Voltage | Main Circuit 12 ... 690 V AC / DC Main Circuit 690 V AC |
| Resistance to Shock acc. to IEC 60068-2-27 | 11 ms Pulse 15g |
| Number of Auxiliary Contacts NC | 0 |
| Maximum Operating Altitude Permissible | 2000 m |
| Rated Operational Current AC-1 | (220 / 240 V) 40 °C 12 A (220 / 240 V) 55 °C 12 A (380 / 440 V) 40 °C 12 A (380 / 440 V) 55 °C 12 A (690 V) 40 °C 6 A (690 V) 55 °C 6 A |
| Standards | IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 |
| Rated Operational Power AC-3 | (220 / 230 / 240 V) 3 kW (400 V) 5.5 kW (400 V) Three Phase 5.5 kW (440 V) 5.5 kW (500 V) 5.5 kW (690 V) 3 kW |
| Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1 | 8 x I _e / AC-3 |

Specifications

| | |
|--|--|
| Horsepower Rating UL/CSA | (208 V AC) Three Phase 3 hp (220 ... 240 V AC) Single Phase 1.5 hp (220 ... 240 V AC) Three Phase 3 hp (440 ... 480 V AC) Three Phase 5 hp (550 ... 600 V AC) Three Phase 5 hp |
| Conventional Free-air Thermal Current | Main Circuit 12 A |
| Rated Frequency | Control Circuit 400 Hz Control Circuit 50 Hz Control Circuit 60 Hz Main Circuit 60 Hz Main Circuit 50Hz Main Circuit DC |
| Rated Short-time Withstand Current | at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 96 A |
| Rated Operational Current AC-3 | (220 / 230 / 240 V) 55 °C 11.3 A (380 / 400 V) 55 °C 11.5 A (440 V) 55 °C 10.1 A (500 V) 55 °C 9.2 A (690 V) 55 °C 3.8 A |
| Rated Making Capacity AC-3 acc. to IEC 60947-4-1 | 10 x I _e / AC-3 |
| Maximum Electrical Switching Frequency | AC-1 300 cycles per hour AC-15 360 cycles per hour AC-3 600 cycles per hour DC-1 600 cycles per hour DC-13 360 cycles per hour DC-3 600 cycles per hour |
| Short-Circuit Protective Devices | gG Type Fuses Type 1&2 25 A |
| Rated Insulation Voltage | 690 V acc. to UL/CSA 600 V |
| Mechanical Durability | 10000000 cycle |
| Coil Operating Limits | (acc. to IEC 60947-4-1) for AC supply 0.85 ... 1.1 x U _c (at $\theta \leq 55^\circ$ C) |
| Secondary Rated Impulse Withstand Voltage | Main Circuit 6 kV |
| Coil Consumption | Average Holding Value 50 Hz 3.5 V - A Average Pull-in Value 50 Hz 3.5 V - A |
| Degree of Protection | Control Circuit Terminals IP20 Main Circuit Terminals IP20 |
| Mounting on DIN Rail | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Screw Terminal Type | Soldering Pins |

Classifications

| | |
|----------|---|
| ETIM 4 | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0 | EC000066 - Power contactor, AC switching |
| ETIM 7 | EC000066 - Power contactor, AC switching |
| ETIM 5.0 | EC000066 - Magnet contactor, AC-switching |
| eClass | 7.0 27371003 |

Dimensions

| | |
|----------------------------|---------|
| Product Net Weight | 0.17 kg |
| Product Net Depth / Length | 51.5 mm |
| Product Net Width | 47.5 mm |
| Product Net Height | 45.5 mm |

Package Information

| | |
|--------------------------------|--------|
| Package Level 1 Width | 108 mm |
| Package Level 1 Height | 69 mm |
| Package Level 1 Depth / Length | 247 mm |

Package Information

| | |
|------------------------------|---------------|
| Package Level 1 EAN | 4013614417115 |
| Package Level 1 Units | 10 piece |
| Package Level 1 Gross Weight | 1.775 kg |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 |
| Customs Tariff Number | 85365080 |