

Representative Image

Catalog No. LRELL11/4X18-G

Description: PVC CTD ELB 90D 1-1/4IN R18IN STL G

UPC No 704508394875

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/4 Inch/35 Metric, Angle 90 Degrees, Radius 18 Inch/457.20 Millimeters, Offset 2 Feet 4 Inch/711.20 Millimeters, Straight End 10 Inch/254.00 Millimeters, Unbent Length 48 Inch/1,219.20 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Length	48 in , 1,219.2 mm
Trade Size	1-1/4 in , 35 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized

by ABB

ETIM	EC001493 Bend for cable protection tubes
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	35 mm
Angle of bow	90 °

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	110787	184105	N/A	2177301	N/A