



Representative Image

## Catalog No. NPL21/2X36-G

**Description:** PVC CTD COND NIPPLE 2-1/2X36IN GRY

**UPC No** 704508013158

**Home > Cable Protection Systems > Ocal > Electrical conduit nipple**

PVC Coated Conduit Nipple, 2-1/2 Inch/63 Metric Pipe Size x 36 Inch/914.4 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

### Descriptors

|                  |                                                      |
|------------------|------------------------------------------------------|
| Category         | Electrical conduit nipple                            |
| Special Features | A Minimum .040 Inch (40 Mil) PVC Coating on Exterior |
| Application      | To Connect Two Fittings                              |

### Specifications

|          |                       |
|----------|-----------------------|
| Material | Steel                 |
| Color    | Gray                  |
| Finish   | Hot-Dipped Galvanized |

### Classifications

|            |                         |
|------------|-------------------------|
| Brand Name | Ocal                    |
| Standard   | cULus E46453, CSA, RoHS |

### Dimensions

|            |                  |
|------------|------------------|
| Length     | 36 in , 914.4 mm |
| Trade Size | 2-1/2 in , 63 mm |

|                                 |                                  |
|---------------------------------|----------------------------------|
| ETIM                            | EC001469 Protective hose adapter |
| With outer thread               | Y                                |
| Thread size outer thread metric | 63                               |
| Material housing                | Other                            |
| Surface protection              | Hot dip galvanized               |
| Model                           | Straight                         |
| Total length                    | 914.4 mm                         |