

## Catalog No. TEY370ST12

**Description:** MCCB 3P 70A W/120-277VAC SHUNT TRIP

**UPC No** 783164196672

**Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers**

The TEY is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEY suitable for varied applications as a lug-lug breaker. All TEY circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEY breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. MCCB 3P 70A W/120-277VAC SHUNT TRIP



Representative Image

### Descriptors

Category	Lighting Panel Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EY

### Specifications

Trip Style	Non-Interchangeable
Poles	3
Amperage	70 A
System Voltage	120 Vac 120/240 Vac 240 Vac 277 Vac
Frame Type	TEY
120 Vac Interrupting Rating	65 KAIC
120/240 Vac Interrupting Rating	65 KAIC
240 Vac Interrupting Rating	65 KAIC
277 Vac Interrupting Rating	14 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Special Markings	HACR
Wire Range (Cu/Al)	14-8 kcmil / 12-8 kcmil
GSA Compliance	No

### Classifications

UL File #	E11592
CSA File#	LR57114

**by ABB**