

## Catalog No. TEYF315ST12

**Description: TEYF 3 POLE 15 AMP W/SHUNT TRIP**

**UPC No 783164388862**

**Home > Circuit Breakers > Molded Case Circuit Breakers > Lighting Panel Circuit Breakers**

The TEYF is a one-inch wide per pole, compact, "bolt-on" circuit breaker for use on grounded 480Y/277 Vac systems. The bolt-on mounting base accessory makes the TEYF suitable for varied applications as a lug-lug breaker. All TEYF circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. TEYF breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. TEYF 3 POLE 15 AMP W/SHUNT TRIP



Representative Image

### Descriptors

|              |                                 |
|--------------|---------------------------------|
| Category     | Lighting Panel Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On)          |
| GO Schedule  | EY                              |

### Specifications

|                                 |  |
|---------------------------------|--|
| Trip Style                      | Non-Interchangeable                              |
| Poles                           | 3  |
| Amperage                        | 15 A   |
| System Voltage                  | 120/240 Vac<br>240 Vac<br>277 Vac<br>480/277 Vac |
| Frame Type                      | TEYF   |
| 120/240 Vac Interrupting Rating | 65 KAIC  |
| 240 Vac Interrupting Rating     | 65 KAIC  |
| 277 Vac Interrupting Rating     | 18 KAIC  |
| 480/277 Vac Interrupting Rating | 18 KAIC  |
| Trip Function                   | LI   |
| Continuous Current Rated        | Standard   |
| Suitable for Reverse Feed       | Yes  |
| Long Time                       | Fixed  |
| Instantaneous                   | Fixed  |
| Current Metering                | No   |
| Protective Relays               | No   |
| Special Markings                | HACR   |
| Wire Range (Cu/Al)              | #14-#10  |
| GSA Compliance                  | No   |

### Classifications

|           |         |
|-----------|---------|
| UL File # | E11592  |
| CSA File# | LR57114 |

**by ABB**