

Representative Image

## Catalog No. THHQB22015

**Description: THHQB MCB 15A 22kA 2P 240V**

**UPC No 783164118421**

**Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 2015 Amps 15 A

### Descriptors

| | |
|---|---|
| Category | Q-Line Miniature Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |
| GO Schedule | EB |

### Specifications

| | |
|---|---|
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 15 A |
| System Voltage | 120 Vac<br>120/240 Vac<br>240 Vac |
| Poles | 2 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 22 KAIC |
| 120/240 Vac Interrupting Rating | 22 KAIC |
| 240 Vac Interrupting Rating | 22 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

### Classifications

| | |
|---|---|
| UL File # | E11592 |

by ABB