



Catalog No. THHQL1120AF2

Description: AFCI 20A CIRCUIT BREAKER

UPC No 783164652857

Home > Circuit Breakers > Residential Circuit Breakers > Arc Fault

Arc fault breakers are designed to detect and prevent damages from arcing caused by damaged wire insulation or a frayed extension cord. All Q Line circuit breakers are one inch wide per pole, compact devices that feature: Quick-make / Quick-break mechanisms, common trip bars, and easy-to-spot trip indications to ensure safety and reliability. AF2 is called a Combination breaker as it protects against arcs in both parallel and series and meets current NEC standards. The THHQL1120AF2 breaker features 1 pole, an ampere rating of 20 A, an interrupting rating of 22kAIC and a voltage rating of 120/240 V.

Descriptors

Category	Arc Fault
GO Schedule	R9

Specifications

Interrupting Capacity Rating	22 kAIC
Voltage	120/240 V
Neutral Connection	Pig Tail
Frame Type	Q-Line
Amperage	20 A
Poles	1
Continuous Current Rated	Standard
120/240 Vac Interrupting Rating	22 KAIC
Instantaneous	Fixed
GSA Compliance	No