



Representative Image

Catalog No. THHQL2150

Description: CIRCUIT BREAKER 2P 50A 120/240V 22KA

UPC No 783164092028

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 2150 Amps 50 A

Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R5

Specifications

Interrupting Capacity Rating	22 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	50 A
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	Yes

Classifications

UL File #	E11592
-----------	--------