

Representative Image

Catalog No. THQB1120

Description: THQB MCB 20A 10KA 1P 120/240V

UPC No 783164012187

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 1120 Amps 20 A

Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EB

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Wire Range (Cu/Al)	14-8 kcmil / 12-8 kcmil
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR SWD
GSA Compliance	No

Classifications

UL File #	E11592

by ABB