



Catalog No. THQB2130GFEP

Description: THQB MCB 30A 10KA 2P 120/240V GFEP

UPC No 783164060249

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. GFEP Amps 30 A

Descriptors

| | |
|--------------|-----------------------------------|
| Category | Q-Line Miniature Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On) |
| GO Schedule | B1 |

Specifications

| | |
|---------------------------------|------------------------|
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 30 A |
| System Voltage | 120 Vac 120/240 Vac |
| Poles | 2 |
| Trip Function | LIG |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Ground Fault | Yes |
| Protective Relays | No |
| Current Metering | No |
| GSA Compliance | No |

Classifications

| | |
|-----------|---------|
| UL File # | E51075 |
| CSA File# | LR10263 |