



Representative Image

Catalog No. THQL1120AF2

Description: AFCI 20A CIRCUIT BREAKER

UPC No 783164652819

Home > Circuit Breakers > Residential Circuit Breakers > Arc Fault

Arc fault breakers are designed to detect and prevent damages from arcing caused by damaged wire insulation or a frayed extension cord. All Q Line circuit breakers are one inch wide per pole, compact devices that feature: Quick-make / Quick-break mechanisms, common trip bars, and easy-to-spot trip indications to ensure safety and reliability. AF2 is called a Combination breaker as it protects against arcs in both parallel and series and meets current NEC standards. The THQL1115 breaker Amps has 1 pole, an ampere rating of 15 A, an interrupting rating of 10 kAIC, and a voltage rating of 120/240V.

Descriptors

Category	Arc Fault
Product Line	Q-Line (Plug-In)
GO Schedule	R9

Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Neutral Connection	Pig Tail
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR SWD
GSA Compliance	Yes

Classifications

UL File #	E11592
-----------	--------