



Representative Image

## Catalog No. THQL1120AF2

**Description: AFCI 20A CIRCUIT BREAKER**

**UPC No 783164652819**

**Home > Circuit Breakers > Residential Circuit Breakers > Arc Fault**

Arc fault breakers are designed to detect and prevent damages from arcing caused by damaged wire insulation or a frayed extension cord. All Q Line circuit breakers are one inch wide per pole, compact devices that feature: Quick-make / Quick-break mechanisms, common trip bars, and easy-to-spot trip indications to ensure safety and reliability. AF2 is called a Combination breaker as it protects against arcs in both parallel and series and meets current NEC standards. The THQL1115 breaker Amps has 1 pole, an ampere rating of 15 A, an interrupting rating of 10 kAIC, and a voltage rating of 120/240V.

### Descriptors

Category	Arc Fault
Product Line	Q-Line (Plug-In)
GO Schedule	R9

### Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Neutral Connection	Pig Tail
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR SWD
GSA Compliance	Yes

### Classifications

UL File #	E11592
-----------	--------