



Representative Image

**Catalog No. THQL1140HM**

**Description: CIRCUIT BREAKER 1P 40A**

**UPC No 783164138290**

**Home > Circuit Breakers > Residential Circuit Breakers > Q Line**

High Magnetic Circuit breakers are designed and programmed to have a higher magnetic trip point than a standard breaker. This can be used in applications where high levels of magnetism may be an issue such as large scale lighting projects. The THQL1140HM breaker features high magnetic trip settings, 1 pole, an ampere rating of 40 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V.

**Descriptors**

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R5

**Specifications**

Specialty Breakers	High Magnetic
Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	40 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

**Classifications**

UL File #	E11592
-----------	--------

