

Representative Image

Catalog No. THQL1120

Description: THQL 1 POLE 120/240V 10K IC 20 AMP

UPC No 783164012866

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R8

Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR SWD
GSA Compliance	Yes

Classifications

UL File #	E11592

by ABB