



Representative Image

Catalog No. THQL1170

Description: CIRCUIT BREAKER 1P 70A

UPC No 783164146271

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL1170 breaker features 1 pole, an ampere rating of 70 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V.

Descriptors

| | |
|--------------|------------------|
| Category | Q Line |
| Product Line | Q-Line (Plug-In) |
| GO Schedule | R5 |

Specifications

| | |
|---------------------------------|------------------------|
| Interrupting Capacity Rating | 10 kAIC |
| Voltage | 120/240 V |
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 70 A |
| System Voltage | 120 Vac 120/240 Vac |
| Poles | 1 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

Classifications

| | |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|