

Representative Image

Catalog No. THQL1130HM

Description: CIRCUIT BREAKER 1P 30A

UPC No 783164138207

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

High Magentic Circuit breakers are designed and programmed to have a higher magnetic trip point than a standard breaker. This can be used in applications where high levels of magnetism may be an issue such as large scale lighting projects. The THQL1130HM breaker features high magnetic trip settings, 1 pole, an ampere rating of 30 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V.

Descriptors

Category	Q Line
Product Line	Q-Line (Plug-In)
GO Schedule	R5

Specifications

Specialty Breakers	High Magnetic
Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	30 A
System Voltage	120 Vac 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E11592

by ABB