



Image représentative

n° de catalogue THQL2120

Description: THQL 2 POLE 120/240V 10K IC 20 AMP

UPC No 783164012910

Accueil > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

THQL 2 POLE 120/240V 10K IC 20 AMP

Descripteurs

| | |
|--------------|-----------------------------------|
| Catégorie | Q-Line Miniature Circuit Breakers |
| Product Line | Q-Line (Plug-In) |
| GO Schedule | R5 |

Spécifications

| | |
|---------------------------------|------------------------|
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 20 |
| System Voltage | 120 Vac 120/240 Vac |
| Poles | 2 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | Yes |

Classifications

| | |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|