


Representative Image

## Catalog No. THQL32070

**Description: CIRCUIT BREAKER 3P 70A 240 10KA**

**UPC No 783164012149**

**Home > Circuit Breakers > Residential Circuit Breakers > Q Line**

Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL32070 breaker features 3 poles, an ampere rating of 70 A, an interrupting rating of 10kAIC, and a voltage rating of 240V.

### Descriptors

| | |
|---|---|
| Category | Q Line |
| Product Line | Q-Line (Plug-In) |
| GO Schedule | R8 |

### Specifications

| | |
|---|---|
| Interrupting Capacity Rating | 10 kAIC |
| Voltage | 240 V |
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 70 A |
| System Voltage | 120 Vac<br>120/240 Vac<br>240 Vac |
| Poles | 3 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| 240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

### Classifications

| | |
|---|---|
| UL File # | E11592 |

by ABB