



Representative Image

Catalog No. TK4V1200R

Description: ENCLOSURE NEMA 3R 1200A

UPC No 783164177626

Home > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Enclosure notes and/or limitation: For 3 phase, 4-wire Ground Fault, order Neutral Kit and Neutral Current Sensor Kit for GF applications (kits must be mounted in enclosure).
 Not suitable for 100% rated 1200 amp Spectra K frame breakers.
 Suitable for parallel 500 kcmil cable maximum.
 Enclosure does not include removable closing cap.
 Order raintight hub separately (requires field cut).

ACCESSORIES:

Neutral Kit (non-GF applications): TNIA800, TNIA1200, TNIA1200C

Neutral Kit(s) (for GF applications): TNIA800G, TNIA1200G

Neutral Current Sensor(s) (for GF applications): TSKG408, TSKG410, TSKG412

Raintight Hubs: TC200, TC250, TC300, TCCP

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA Type 3R
Mounting	Surface
Frame Type	K1200 SK1200
Amperage	1200 A
Material	Steel
GSA Compliance	No

Classifications

UL/CUL Listing	CSA UL
----------------	-----------

Dimensions

Height	47.75 in
Depth	8.31 in
Width	22.56 in

Dimensions

Weight

112.71 lb