



Representative Image

Catalog No. TLM1212CCU

Description: 12 CIR. 125 A CONVERTIBLE L/C

UPC No 783164112313

Home > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM1212CCU features space for 12, 1" breakers, a 125 A bus ampere rating, a copper bus, and a combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	12
1" Space	12
1/2" Space	24
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	Yes
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Height	19.0 in
Weight	19.2 lb

by ABB

Dimensions

Width

14.0 in

Publications

Title	Publication No.	Publication Type
PowerMark Gold 100-125A, 12/24 Circuit Load Center		
PowerMark Gold 100-125A, 12/24 Circuit Load Center	DET-582	Application and Technical

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.