



Catalog No. TLM1612CCU

Description: FLD CNVRTB 125A 16CRK 22K IC COMB

UPC No 783164156737

Home > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM1612CCU features space for 16, 1" breakers, a 125 A bus ampere rating, a copper bus, and a combination/flush enclosure.



Representative Image

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

Load Center Type	Standard
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Amperage	125 A
Device type	Main Lug
Enclosure	Indoor
Phase	1 Phase
1" Space	16
1/2" Space	16
Feed	Either
Door	Yes
GSA Compliance	Yes
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 1
Factory Installed Ground Kit	No
Enclosure Type	Indoor, Combination
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----



Publications

Title	Publication No.	Publication Type
Section 1 BuyLog: Load centers and associated circuit breakers Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.	DET1023	Application and Technical

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.