



Catalog No. TM815RCUFL

Description: 150A 8CT 22K IC 3R SUBFEED MAIN

UPC No 783164113242

Home > Load Centers > Load Centers

Main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM815RCUFL features spaces for 8, 1" breakers, a 150A main ampere rating, a copper bus, factory installed feed-through lugs, and an outdoor suitable enclosure.



Representative Image

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

Load Center Type	Standard
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	150 A
Device type	Main Breaker
Enclosure	Outdoor
Phase	1 Phase
1" Space	8
1/2" Space	16
Feed	Top
Door	No
GSA Compliance	No
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 3R
Factory Installed Ground Kit	No
Enclosure Type	Outdoor, Surface Mount
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----



Publications

Title	Publication No.	Publication Type
Section 1 BuyLog: Load centers and associated circuit breakers Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.	DET1023	Application and Technical

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.