



Representative Image

## Catalog No. TXQL2120

**Description:** CIRCUIT BREAKER 2P 20A

**UPC No** 783164024791

**Home > Circuit Breakers > Residential Circuit Breakers > Q Line**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 2120 Amps 20 A

### Descriptors

Category	Q Line
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	R5

### Specifications

Interrupting Capacity Rating	65 kAIC
Voltage	120/240 V
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	65 KAIC
120/240 Vac Interrupting Rating	65 KAIC
Suitable for Reverse Feed	Yes
Wire Range (Cu/Al)	14-8 kcmil / 12-8 kcmil
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------