



Representative Image

Ref. No. 673328 | Catalog No. EP102UCC25
Description: Miniature circuit breaker EP100UC 2P 25A C
EAN 5413656733287
Home > Modular DIN-rail devices > Circuit Protection > MCB DIN-rail

- **Safe and reliable**
- Clear print
- High degree of insulation IP20
- Padlocking toggle
- Sealed terminals
 - **User friendly**
 - **Multifunctional**
- Motor operator : same device left and right assembly
- Common device for all products
 - Shunt trip and under voltage relay
- Auxiliaries
 - **Easy to install**
- >Different connection techniques
- High torque performance 4.5 Nm
- High capacity terminals 35mm²

Descriptors

Category	MCB DIN-rail
Family	Circuit protection

Specifications

In (A)	25
Number of Poles	2P
Number of modules	2
Switching off curve	C (5-10 In)
Group	ElfaPlus
Range	Commercial - Industrial
Switch	EP100 UC : 6kA - AC/DC
Connections- Top	Screw
Connections- Bottom	Screw
Standards	10kA industrial BS EN 60947-2 6kA domestic BS EN 60898
AC/DC	AC/DC
Logo	GE
Rated Voltage (V)	230 V / 400 V
Short-circuit capacity (kA)	6
Selectivity class	3
Terminal capacity max (mm ²)	25-35 mm ²
Electrical service life	20000/10000
Minimum operating voltage Ubmin (V)	12 V
Terminal capacity min (mm ²)	0.75 / 1 mm ²
Tropicalisation	95%RH at 55°C

Classifications

Approvals	CE VDE
ETIM 5.0	EC000042 - Miniature circuit breaker (MCB)
ETIM 6.0	EC000042 - Miniature circuit breaker (MCB)

Dimensions

Weight	0.250 kg
--------	----------

Package Information

Standard packing	6
------------------	---

Operating Performance

Operating temperature	-25°C / 55°C
-----------------------	--------------