



Representative Image

**Ref. No. 686766 | Cat. No. EP62ULD40**
**Description: MCB Miniature circuit breaker ElfaPlus EP60 UL 2P 40A D GE**
**EAN 5413656867661**
**Home > Modular DIN-rail devices > Circuit Protection > MCB DIN-rail**

- **Safe and reliable**
- Clear print
- High degree of insulation IP20
- Padlocking toggle
- Sealed terminals
  - **User friendly**
  - **Multifunctional**
- Motor operator : same device left and right assembly
- Common device for all products
  - Shunt trip and under voltage relay
- Auxiliaries
  - **Easy to install**
- >Different connection techniques
- High torque performance 4.5 Nm
- High capacity terminals 35mm<sup>2</sup>

**Descripteurs**

Catégorie	MCB DIN-rail
Family	Circuit protection

**Spécifications**

In (A)	40
Number of Poles	2P
Number of modules	2
Switching off curve	D (10-20 In)
Group	ElfaPlus
Range	Commercial - Industrial Residential
Switch	EP60 UL : 6kA - Recognized UL1077
Connections- Top	Screw
Connections- Bottom	Screw
Standards	10-20kA industrial BS EN 60947-2 6kA domestic BS EN 60898
AC/DC	AC
Logo	GE
Rated Voltage (V)	277 V / 480 V
Short-circuit capacity (kA)	6
Selectivity class	3
Terminal capacity max (mm <sup>2</sup> )	25-35 mm <sup>2</sup>
Electrical service life	20000/10000
Minimum operating voltage U <sub>bmin</sub> (V)	12 V
Terminal capacity min (mm <sup>2</sup> )	0.75 / 1 mm <sup>2</sup>
Tropicalisation	95%RH at 55°C


  
**by ABB**

## Classifications

Approvals	CE CSA EAC UR VDE
ETIM 5.0	EC000042 - Miniature circuit breaker (MCB)
ETIM 6.0	EC000042 - Miniature circuit breaker (MCB)

## Dimensions

Weight	0.250 kg
--------	----------

## Package Information

Standard packing	6
------------------	---

## Operating Performance

Operating temperature	-25°C / 55°C
-----------------------	--------------